

7700268 MicroSicuro CR/A-R Multi-Use Mop for Cleanroom

**Individualization
on request!**

NEW



Product description

Sustainable reusable mop for sterile GMP areas.

- Made from 100 % polyester micro loops
- Not for disinfectants containing chlorine
- Ideal for loosening adhering dirt
- Ideally suited for the EasyMop® GMP and CR pre-preparation method and Ringo GMP flat wringer
- Autoclavable

**MADE IN
GERMANY**



ISO	3	4	5	6	7	8
GMP			A/B		C	D

Product specifications

Article name Article number	MicroSicuro CR/A-R 7700268
Dimensions Weight	40 x 12 cm 111.9 g
Working material (colour)	100% polyester (white/green)
Absorbent material	100% polyester (white)
Backing material (colour)	100% polyester (white)
Edge material (colour)	100% polyester (white)
Pocket System Pocket System material (colour)	EasyFlow Bag 100% polyester (white)
Chemical compatibility	Resistant to a large number of commercially available cleaning chemicals, except acids, chlorinated compounds, alkalis and bleaching agents.
Sterility	Autoclavable (121 °C for 20 minutes)
Re-use	Depending on the intended use, up to 50 cycles of sterile reprocessing
Recycling rate	76 %
Care instructions	Please note the care instructions in the downloads.
Storage	The general storage conditions apply: Protect from harmful influences (liquids, sun or UV light, contamination, pressure) and store at recommended temperature 5-40°C.
Selling unit	1 PU
Quantity in carton	100 Pieces
Carton weight	11.19 kg
Cartons per pallet Pallet	no pallet shipment 120 x 80 x 220 cm
Packaging note	The size of the packaging, as well as the quantity in the box, may vary depending on the order quantity and the volume of other products ordered.
Customs tariff number	63071090
Country of origin	Germany
EAN-Number	4065237109212
Compatible accessories	Our sales department will be happy to advise you on suitable accessories

Compatible methods Cleaning area

- MopScoop®
- MopFloat®
- EasyMop®
- Flat wringer Ringo®



Industry Sectors

Preparation Recycling

This classification is a non-binding recommendation. The user must check the individual suitability and compatibility for his individual area of application. The condition of the material must be checked regularly; damaged products must be replaced immediately. All information without guarantee. Subject to changes and deviations.